

MODLIGHT ILLUMIX CLASSIC LINE

EXCELLENT LIGHTING FOR ANY JOB

The LED machine light Illumix Classic Line has an M12 port and displays its strengths in harsh, industrial environments:

It is robust and provides perfect illumination in daylight quality. The compact, alluminium design allows this product to be used in small spaces, so it can be mounted in almost any machine or system.

- Protected IP67 – suitable for use in environments with coolants and lubricants, flying sparks or shavings
- Extremely high daylight quality lighting (105 lm/W)
- Energy-saving LED technology – maintenance-free and durable
- Rotatable mounting brackets
- Fast and secure mounting



	Modlight Illumix Classic Line 6 W	Modlight Illumix Classic Line 12 W	Modlight Illumix Classic Line 18 W	Modlight Illumix Classic Line 24 W
Order data	Item no. 4000-75801-1415006	Item no. 4000-75801-1415012	Item no. 4000-75801-1415018	Item no. 4000-75801-1415024
Technical Data				
Dimensions (HxWxD)	37 x 40 x 235 mm	37 x 40 x 410 mm	37 x 40 x 585 mm	37 x 40 x 760 mm
Power and rated voltage	6 W/24 V DC	12 W/24 V DC	18 W/24 V DC	24 W/24 V DC
Luminaire light current	630 lm	1260 lm	1890 lm	2520 lm
Accessories				
M12 cordset	Female, 4-pin, depending on cable no. (xxx) and length (yyy) 7000-12221-xxxyyy			

MODLIGHT ILLUMIX SLIM LINE

EXCELLENT LIGHTING FOR ANY JOB

The LED machine light Modlight Illumix Slim Line has an M8 port and provides perfect daylight quality.

The compact design allows this product to be used in small spaces so it can be perfectly mounted in almost any machine or system.



- Extremely high daylight quality lighting (105 lm/W)
- Energy-saving LED technology – maintenance-free and durable
- Protected IP54 – for use in the field of industrial and plant engineering
- Rotatable mounting brackets
- Fast and secure mounting

	Modlight Illumix Slim Line 4W	Modlight Illumix Slim Line 8W	Modlight Illumix Slim Line 16W	Modlight Illumix Slim Line 24W	Modlight Illumix Slim Line 32W
Order data	Item no. 4000-75800-1715004	Item no. 4000-75800-1715008	Item no. 4000-75800-1715016	Item no. 4000-75800-1715024	Item no. 4000-75800-1715032
Technical Data					
Dimensions (HxWxD)	34 x 24 x 218 mm	34 x 24 x 358 mm	34 x 24 x 638 mm	34 x 24 x 918 mm	34 x 24 x 1198 mm
Power and rated voltage	4 W/24 VDC	8 W/24 VDC	16 W/24 VDC	24 W/24 VDC	32 W/24 VDC
Luminaire light current	420 lm	840 lm	1680 lm	2520 lm	3360 lm
Accessories					
M8 cordset	Female, 4-pin, depending on cable no. (xxx) and length (yyyy) 7000-08061-xxxxyyy				