COMPACT

SYSTEM SOLUTIONS FROM A SINGLE SUPPLIER

48 V DC POWER MANAGEMENT


Murrelektronik's 48 V DC power management system is ideal for powering machines and systems. Its primary focus is on maximum machine uptime. The system includes not only high performance power supply units but also buffer modules and electronic current monitoring units.

POWER

MANAGEMENT BENEFITS

- Complementary products
- Worldwide applications
- Consistent mounting style
- Maximum system availability
- EMC protection

48 V POWER MANAGEMENT





stay connected

For more information about Murrelektronik and our products visit **www.murrelektronik.com**

or scan the QR code below....



COMPACT



ONE SOURCE FITS ALL

Murrelektronik is the only company that offers an integrated power management system for 48 VDC. This includes power supply units, buffer modules and electronic current monitoring units that, when working together, ensure machine uptime and maximum EMC protection.



POWER SUPPLY UNITS

Evolution+ 48 V DC, 3-phase, 3 x 360...520 V AC

- Continuous 2-phase operation
- Spring clamp terminals
- Varnished circuit board
- N/O contact

BUFFER MODULE



Emparro Cap 48 V DC

- Maintenance-free for life thanks to ultra capacitors
- Slimmest 48 V buffer module in the world
- LED indicators
- N/O contact

Emparro 48 V DC, single phase 100...240 V AC

- Up to 95 % efficiency rating
- 150 seconds Power Boost for up to 4 seconds
- Derating from 60 °C
- N/O contact
- MTBF up to 624,000 h

ELECTRONIC CURRENT MONITORING



MICO+ 48 V DC

- Optimum tripping time
- Spring clamp terminals
- Temperature independent tripping time
- Alarm contact & remote restart

ORDERING DATA

Power Supply	Current	Art. No.
Evolution+ 48 V DC, 3-phase, 360520 V AC	5 A	85009
	10 A	85010
	20 A	85011
Emparro 48 V DC, single phase, 100240 V AC	2.5 A	85437
	5A	85438
	10 A	85439
Buffer Module		
Emparro Cap 48 V DC	20 A – 0.1 sec	85459
Electronic Current Monitoring	Current adjustment	
MICO+ 48 V DC	1, 2, 3, 4 A	9000-42084-0100400
	1, 2, 4, 6 A	9000-42084-0100600

