# COMPACT



MURRELEKTRONIK VALVE PLUGS

### **MORE VARIETY**

### THAN EVER

20 years ago, Murrelekronik developed and produced the first prewired and molded valve plug. It was a revolution! And because Murrelektronik has continuously improved the valve plugs, they have enjoyed long-running success, today more than ever. A captive gasket, integrated LED status indicator and suppression are the top features of Murrelektronik's MSUD valve plug.



### **ATTRACTIVE ATTRIBUTES**

- 100 % tested ensures top process reliability
- State-of-the-art potting technology absolutely resistant to shock and vibration
- Captive gasket in signal green sealed according to IP65 and IP67
- Pre-wired cables for easy installation
- Available as bridge rectifier, adapter, switching amplifier and much more



### VALVE PLUGS' SELLING FEATURES...

- A captive screw
- CSA and ATEX approvals
- Large selection: four cable materials with three colors each

#### **DID YOU KNOW?**

Murrelektronik's double valve plugs reduce your installation efforts. With one cable you can control two valves independently. This saves installation time and real cash. They are an excellent choice and are available in forms A, B, BI, C and CI (18, 10, 11, 8 and 9.4 mm).





## **COMPACT**



### THE LATEST INNOVATIONS

***	1-	l		
M8	Туре	Length (in mm)	Form C	Form CI
E A Michigan	Adapter with M8 connector on the back	_	7000-88975-0000000	7000-88995-0000000
	Adapter with M8 connector on the top	_	7000-88965-0000000	7000-88985-0000000
	Double valve plug with M8 connector on the back	100 150 200	7000-89211-6260000 7000-89221-6260000 7000-89231-6260000	7000-89271-6260000 7000-89281-6260000 7000-89291-6260000
	Double valve plug with M8 connector on the top	100 150 200	7000-89181-6260000 7000-89191-6260000 7000-89201-6260000	7000-89241-6260000 7000-89251-6260000 7000-89261-6260000
M12	Туре	Length (in mm)	Form C	Form CI
	Adapter with M12 connector on the back	_	7000-42831-0000000	7000-42871-0000000
	Adapter with M12 connector on the top	_	7000-42811-0000000	7000-42851-0000000
	Double valve plug with M12 connector on the back	100 150 200	7000-42911-6260000 7000-42921-6260000 7000-42931-6260000	7000-42971-6260000 7000-42981-6260000 7000-42991-6260000
	Double valve plug with M12 connector on the top	100 150 200	7000-42881-6260000 7000-42891-6260000 7000-42901-6260000	7000-42941-6260000 7000-42951-6260000 7000-42961-6260000
Open Ended Wires	Туре	Length	Form C	Form CI
	Double valve plug with open ended wires	100 150 200	7000-58401-6270300 7000-58411-6270300 7000-58421-6270300	7000-58431-6270300 7000-58441-6270300 7000-58451-6270300